



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHU4N9NS Unmetered 30/20 WRTR

Eaton Corp

Catalog Number	CHU4N9NS
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Unmetered, Water and Tamper Resistant Center Receptacle, Unmetered, 30A, 20A, None, Non-Ground Fault, Non-Ground Fault, None, Top, Surface, Circuits: 4, Nema TT-30R, Nema 5-20R2GFI (3), None, 3, 3, 0, 125V, 125V, None
Weight per unit	15.0 (lbs/each)
Product Category	20191211090026

Features

dimensions	18.2500 IN X 10.2500 IN X 8.0000 IN
Mounting Type	Surface

Dimensions and Weight

Height	8.0000
Length	18.2500
Width	10.2500

Descriptions

Description	UNMETERED 30/20 WRTR
extra long description	ETN CHU4N9NS UNMETERED, 30/20, WRTR
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount unmetered, Water and tamper resistant center receptacle, Unmetered, 30A, 20A, None, Non-ground fault, Non-ground fault, None, Top, Surface, Circuits: 4, NEMA TT-30R, NEMA 5-20R2GFI (3), None, 3, 3, 0, 125V, 125V, None
Product Type	Unmetered, 30/20, WRTR
Special Features	Water and tamper resistant center receptacle

Manufacturer Information

Brand	Eaton
GTIN	00786685406350
Manufacturers Part Number	CHU4N9NS
UPC	786685406350

Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount unmetered



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	15

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	SURFACE
standard	UL 231,UL Listed file E163588