

Eaton CHU602G2GKGSX

Catalog Number: CHU602G2GKGSX

Eaton pedestal mount unmetered, Unmetered, 60A Main, 20A, 20A, 20A, Ground fault, Ground fault, Ground fault, Top, Surface, Circuits: 6, NEMA 5-20R2 WR, NEMA 5-20R2 WR, NEMA 6-20R2 WR, 3, 3, 3, 125V, 125V, 250V



Photo is representative

General specifications

Product Name	Catalog Number
Eaton pedestal mount unmetered	CHU602G2GKGSX
UPC	Product Length/Depth
786689528294	6.8 in
Product Height	Product Width
7.6 in	9.5 in
Product Weight	Certifications
15.8 lb	UL Listed

defaultTaxonomyAttributeLabel

Type

Unmetered

Circuit breaker position 1

Ground fault

Circuit breaker position 2

Ground fault

Circuit breaker position 3

Ground fault

Receptacle center

NEMA 5-20R2 WR

Receptacle left

NEMA 5-20R2 WR

Receptacle right

NEMA 6-20R2 WR

Mounting

Surface

Number of circuits

6

Resources

Specifications and datasheets

[Eaton Specification Sheet - CHU602G2GKGSX](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)