

## Eaton pedestal mount unmetered

**CHU6G6G5GS**

**UPC:**782114203927

**Dimensions:**

- **Height:** 17.1 IN
- **Length:** 4.3 IN
- **Width:** 9.5 IN

**Weight:**16.25 LB

**Warranties:**

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

**Specifications:**

- **Type:** Unmetered
- **Circuit Breaker Position 1:** Ground fault
- **Feed Type:** Top
- **Mounting:** Surface
- **Number Of Circuits:** 4
- **Receptacle Center:** NEMA 5-20R2
- **Receptacle Right:** NEMA 6-20R2

**Supporting documents:**

- [Dimensional Drawing - POWER OUTLET, SURFACE MOUNT, UNMETERED](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CHU6G6G5GS](#)

**Certifications:**

- UL Listed file E163588
- UL 231

**Product compliance:** No Data

---



## Eaton pedestal mount unmetered

**CHU6G6G5GS**

**UPC:**782114203927

**Dimensions:**

- **Height:** 17.1 IN
- **Length:** 4.3 IN
- **Width:** 9.5 IN

**Weight:**16.25 LB

**Warranties:**

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

**Specifications:**

- **Type:** Unmetered
- **Circuit Breaker Position 1:** Ground fault
- **Feed Type:** Top
- **Mounting:** Surface
- **Number Of Circuits:** 4
- **Receptacle Center:** NEMA 5-20R2
- **Receptacle Right:** NEMA 6-20R2

**Supporting documents:**

- [Dimensional Drawing - POWER OUTLET, SURFACE MOUNT, UNMETERED](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CHU6G6G5GS](#)

**Certifications:**

- UL Listed file E163588
- UL 231

**Product compliance:** No Data

---

