

# Eaton CHU9N9NKGS

Catalog Number: CHU9N9NKGS

Eaton pedestal mount unmetered, 20A, 20A, 20A, Non-ground fault, Non-ground fault, Ground fault, Top, Surface, Circuits: 4, NEMA 5-20R2GFI WRTR, NEMA 5-20R2GFI WRTR, NEMA 6-20R2 WR, 3, 3, 3, 125V, 125V, 250V

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton pedestal mount unmetered	CHU9N9NKGS
<b>UPC</b>	<b>Product Length/Depth</b>
786689321314	6.7 in
<b>Product Height</b>	<b>Product Width</b>
7.5 in	9.5 in
<b>Product Weight</b>	<b>Certifications</b>
14.2 lb	UL Listed file E163588 UL 231

## defaultTaxonomyAttributeLabel

### Special features

Pedestal mount

### Type

Unmetered

### Circuit breaker position 1

Non-ground fault

### Circuit breaker position 2

Non-ground fault

### Circuit breaker position 3

Ground fault

### Receptacle center

NEMA 5-20R2GFI WRTR

### Receptacle left

NEMA 5-20R2GFI WRTR

### Receptacle right

NEMA 6-20R3

### Feed type

Top

### Mounting

Surface

### Number of circuits

4

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - CHU9N9NKGS](#)