

DATE: LOCATION: TYPE: PROJECT: CATALOG #:

tradeSELECT[®]

FEATURES

- LED life-cycle of more than 10 years
- Quick installation
- Damp Location Listed 20°C to 30°C (68°F to 86°F)
- Fully adjustable lamp-heads
- Wall or Ceiling mount



SPECIFICATIONS

DESCRIPTION

- The CIR Series offers quality and value with a compact and attractive LED based remote emergency light
- The white or black base-plate and lampheads are made of high impact UL flame rated thermoplastic
- Lamp-heads are fully adjustable and glare-free
- The remote lamps are driven by the Compass remote capacity Exit, Combo or Emergency Light

APPLICATION

 The CIR Series can be applied in stair-wells, hallways, offices and other commercial applications

COMPLIANCES

- UL924 Listed for Damp Location
- NFPA 101 and NFPA 70
- OSHA



WARRANTY

• 2 year full unit warranty





ORDERING GUIDE


Catalog Number	Description	Voltage	Lamp Watts (Each)
CIRS	Single LED remote white lamp-head with mounting base	3 VDC	1 Watt
CIRD	Double LED remote white lamp-head with mounting base	3 VDC	1 Watt
CIRSB	Single LED remote black lamp-head with mounting base	3 VDC	1 Watt
CIRDB	Double LED remote black lamp-head with mounting base	3 VDC	1 Watt


*Powered by the Compass Exit, Combo or Emergency Light with Remote Capacity

DIMENSIONS









Current 🗐

currentlighting.com/compass

© 2022 HLI Solutions, Inc. All rights reserved. Information and specifications subject to change without notice. All values are design or typical values when measured under laboratory conditions.