

Simplified installation.



The CJB Integrated JBox Downlight gives you the freedom to add a fixture where you want, while maintaining an attractive, consistent look. It installs easily just about anywhere. There's no need to attach a junction box – it's already attached to the fixture. This slim LED downlight features two mounting options: fast installation directly into the ceiling with no housing needed or as an LED trim into an existing housing in retrofit situations.



Series Consideration

Product Features

- Slim 4" and 6" LED recessed downlight with attached driver and JBox
- 2-in-1 Version: Installs canless or converts to fit most 4" or 6" housings
- 5 Color Field-SeleCCTable: 2700K, 3000K, 3500K, 4000K, 5000K
- · Wet location listed for showers or covered outdoor locations
- 4" delivers 600 lumens; 6" delivers 900 lumens
- 5% Phase Cut (LE/TE) Dimming (with compatible dimmers)
- Included: LED Fixture, E26 medium socket adapter, & mounting hardware: (4"-friction blades; 5/6"-torsion springs)
- Specs: 35,000 hrs, 90+ CRI, 120V input, ENERGY STAR®, Air-tite, IC-Rated
- 5-year Warranty

A slim 2-in-1 installation LED downlight with integral driver and JBox suitable for fast installation directly into a ceiling with no housing needed, or retrofit as an LED Trim into an existing housing.



Catalog Number	Material Number	Description	UPC	Accessories			
				Mounting Frames		Mounting Frames w/Drywall Collar	
Basic version Canless installation only					HL6RSMF 6"	MF4RC 4"	MF6RC 6"
CJB4069FS1EMW	13627542	4" CJB, 600lm, 5CCT, Canless Only	080083266234	•		•	
CJB6099FS1EMW	13627543	6" CJB, 600lm, 5CCT, Canless Only	080083266258		•		•
CJB4069FS1EMW-6PK	13627544	4" CJB, 600lm, 5CCT, Canless Only, 6 Pack	080083266272	•		•	
CJB6099FS1EMW-6PK	13627545	6" CJB, 600lm, 5CCT, Canless Only, 6 Pack	080083266296		•		•
CJB4069FS1EMW-12PK	13627546	4" CJB, 600lm, 5CCT, Canless Only, 12 Pack	080083266418	•		•	
CJB6099FS1EMW-12PK	13627547	6" CJB, 600lm, 5CCT, Canless Only, 12 Pack	080083266432		•		•

Dual Installation version 2-in-1 Canless or Can (Recessed LED Trim)

CJB4069FS1EMWR	13627549	4" CJB, 600lm, 5CCT, Dual Installation	080083266470	•		•	
CJB6099FS1EMWR	13627560	6" CJB, 600lm, 5CCT, Dual Installation	080083266494		•		•
CJB4069FS1EMWR-6PK	13627561	4" CJB, 600lm, 5CCT, Dual Installation, 6 Pack	080083266517	•		•	
CJB6099FS1EMWR-6PK	13627562	6" CJB, 600lm, 5CCT, Dual Installation, 6 Pack	080083266531		•		•
CJB4069FS1EMWR-12PK	13627563	4" CJB, 600lm, 5CCT, Dual Installation, 12 Pack	080083266555	•		•	
CJB6099FS1EMWR-12PK	13627564	6" CJB, 600lm, 5CCT, Dual Installation, 12 Pack	080083266579		•		•


















Refer to ENERGY STAR® Certified Products List.
Can be used to comply with California Title 24 High Efficacy requirements
Certified to California Appliance Efficiency Database under JA8.







CJB6099FS1EMW installed in mounting frame


6"

Canless





OR



Lighting Brands

Ametrix AtLite

Corelite Ephesus Fail-Safe HALO

HALO Commercial

Invue iO Iris Lumark Lumière McGraw-Edison

Metalux MWS Neo-Ray Portfolio

PrentaLux - 3D Printed Lighting

RSA Shaper Streetworks Sure-Lites Telensa

Controls Brands

Greengate Fifth Light

Intelligent Lighting Controls

Connected Lighting Systems and Smart Spaces Platform

WaveLinx



