

Eaton Classified 3/4" thermal magnetic circuit breaker

CL120

UPC:786676011556

Dimensions:

- **Height:** 3 IN
- **Length:** 3 IN
- **Width:** 1 IN

Weight: .3 LB

Notes: Replacement for Square D Homeline, GE Type THQ, Crouse-Hinds Type MP, Thomas and Betts Type TB, Murray Type MP, ITE/Siemens Type QP. Requires 1-inch (25.4 mm) space.

Warranties:

- Limited lifetime residential, 1 year commercial

Specifications:

- **Type:** Type CL 1-Inch classified replacement breaker
- **Amperage Rating:** 20A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240 V
- **Main Circuit Breaker:** CL
- **Wire Size:** #14-4 AWG Cu/Al
- **Circuit Breaker Type:** CH
- **Used With:** Type CH Loadcenters

Supporting documents:

- [Loadcenters and Circuit Breakers](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CL120](#)

Certifications:

- UL 489

Product compliance: No Data



