

Eaton Classified 1" AFCI circuit breaker

CL120CAF

UPC:786685271514

Dimensions:

- **Height:** 1.25 IN
- **Length:** 3 IN
- **Width:** 4.75 IN

Weight: .53 LB

Notes: Replacement for Square D Homeline, GE Type THQ, Crouse-Hinds Type MP, Thomas and Betts Type TB, Murray Type MP, ITE/Siemens Type QP. Requires 1-inch (25.4 mm) space.

Warranties: No Data

Specifications:

- **Special Features:** Combination arc fault
- **Amperage Rating:** 20A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240V
- **Main Circuit Breaker:** CL
- **Wire Size:** #14-4 AWG Cu/Al
- **Used With:** Type CH Loadcenters

Supporting documents:

- [Eaton's Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CL120CAF](#)

Certifications:

- UL 489

Product compliance: No Data



Eaton Classified 1" AFCI circuit breaker

CL120CAF

UPC:786685271514

Dimensions:

- **Height:** 1.25 IN
- **Length:** 3 IN
- **Width:** 4.75 IN

Weight: .53 LB

Notes: Replacement for Square D Homeline, GE Type THQ, Crouse-Hinds Type MP, Thomas and Betts Type TB, Murray Type MP, ITE/Siemens Type QP. Requires 1-inch (25.4 mm) space.

Warranties: No Data

Specifications:

- **Special Features:** Combination arc fault
- **Amperage Rating:** 20A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240V
- **Main Circuit Breaker:** CL
- **Wire Size:** #14-4 AWG Cu/Al
- **Used With:** Type CH Loadcenters

Supporting documents:

- [Eaton's Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CL120CAF](#)

Certifications:

- UL 489

Product compliance: No Data

