



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CL250 Type CL BRKR 50A/2POLE 120/240V 10K-Classified 1"

Eaton Corp

Catalog Number	CL250
Manufacturer	Eaton Corp
Description	Standard Trip Circuit Breaker, 50 A, Common Tripping Mechanism, Plug-On, 120/240 V Ac, 3 In Overall Height, 3 In Overall Length, 2 In Overall Width
Weight per unit	0.5000 (lbs/each)
Product Category	2 Pole Standard Trip Plug-In

Features

amperage rating	50 A
dimensions	3.0000 IN X 2.0000 IN X 3.0000 IN
Poles	Two-pole
Trip Type	Common breaker trip

Descriptions

Description	TYPE CL BRKR 50A/2POLE 120/240V 10K-CLASSIFIED 1"
extra long description	ETN CL250 CL bkr 50A/2Pole 120/240V

Manufacturer Information

GTIN	00786676011693
UPC	786676011693

Taxonomies, Classifications, and Categories

Category Description	CLASSIFIED BREAKERS
Type	3/4" Thermal magnetic circuit breakers

Packaging

Carton	5
Package	25
Weight Per each	0.5

Uses, Certifications, and Standards

Application	Generation - Conventional Energy - Conventional EnergyOtherGeneration - Renewable Energy - Alternative EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - Other
standard	UL 489