

Eaton CL250

Catalog Number: CL250

Eaton Classified 3/4" thermal magnetic circuit breaker, Type CL 1-Inch classified replacement breaker, 50 A, 10 kAIC, Two-pole, 120/240V, CL, Common breaker trip, #14-4 AWG Cu/Al, CL, Type CH Loadcenters

General specifications



Product Name	Catalog Number
Eaton Classified 3/4" thermal magnetic circuit breaker	CL250
	UPC
	786676011693

Product Length/Depth	Product Height
3 in	3 in

Product Width	Product Weight
2 in	0.5 lb

Warranty	Certifications
Limited lifetime residential, 1 year commercial	UL 489

Catalog Notes
Replacement for Square D Homeline, GE Type THQ, Crouse-Hinds Type MP, Thomas and Betts Type TB, Murray Type MP, ITE/Siemens Type QP.
Requires Two 1-inch (25.4 mm) spaces.

defaultTaxonomyAttributeLabel

Type

Type CL 1-Inch classified replacement breaker

Amperage Rating

50 A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

CH

Used with

Type CH Loadcenters

Interrupt rating

10 kAIC

Main circuit breaker

CL

Wire size

#14-4 AWG Cu/Al

Number of poles

Two-pole

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

[Standard circuit breaker catalog numbers - 5651B63SH09](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CL250](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)