

# Eaton CLNSURGE

Catalog Number: CLNSURGE

Eaton Type CL circuit breaker surge protective device, Plug On Surge Protective Device UL Classified

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Type BR plug on module surge protection device	CLNSURGE
	<b>UPC</b>
	786689353698
<b>Product Length/Depth</b>	<b>Product Height</b>
3.071 in	2.981 in
<b>Product Width</b>	<b>Product Weight</b>
1.98 in	1 lb
<b>Certifications</b>	
UL 1449	
cUL Certified	



## Product specifications

### Short-circuit rating

10 kA

### Type

Type BR

### Frequency rating

50/60 Hz

### Maximum continuous operating voltage

150 V L-N, 300 V L-L

### Surge current

18 kA

### Protection

L-N, L-L

### Nominal Discharge Current

3 kA

### Measured limiting voltage

600 V

## Resources

### Brochures

[Product Family Guide](#)

[Eaton Solutions, Publication No. SA00404006E / VCG1302](#)

[Complete Home Protection, Publication No. FL010001EN / 3PC](#)

[Eaton Surge Module Product Aid](#)

[Complete Home Protection, Publication No. BR00414002E / VCG1502](#)

### Installation instructions

[Classified Surge Module IL](#)

### Specifications and datasheets

[Eaton Specification Sheet - CLNSURGE](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)