



Catalog Number	
Notes	
Туре	

Contractor Select[™] **CM** Series Ceiling Mount Sensor

The CM is a low voltage sensor that easily mounts directly to a ceiling tile or a metallic grid. Lens options include large motion extended range and small motion standard range.

FEATURES:

- PIR Occupancy Detection
- 360° Coverage
- Up to 14 Sensors per Power Pack
- Time Delay: 30 sec to 20 min
- No Minimum Load Requirements
- Push-Button Programmable
- Green LED Indicator
- 100 Hr. Lamp Burn-in Timer Mode



Catalog Number	UPC	Decription	Detection Type	Coverage	Voltage Type	Color	Voltage	Pallet Quantity
CM 9	745975808304	Ceiling Mount Sensor	Passive Infrared (PIR)	Small Motion 360°	Low	White	12 to 24V	96

More configurations are available. Click here or visit www.acuitybrands.com and search for CM Series.





Specifications

INSTALLATION:

Suitable for mounting directly to a ceiling tile or a metallic grid (two self-tapping screws provided). Sensor's mounting holes also align with 3.5" octagon or single gang handy box (screws not provided). Sensor will detect motions crossing segments more effectively than motions parallel to beams.

LISTINGS:


CSA certified to US and Canadian safety standards. For use in ambient operating temperatures ranging from -10°C to 85° C.

WARRANTY:

5-year limited warranty. Complete warranty terms located at: www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

Note: Actual performance may differ as a result of end-user environment and application. Specifications subject to change without notice.

Dimensions



All dimensions are inches (centimeters) unless otherwise indicated.