

# Eaton CN15DN3AB

Catalog Number: CN15DN3AB

Eaton Freedom NEMA motor control contactor, NEMA Freedom Series Non-Reversing contactor, 2 hp at 115V, 3 hp at 230V, 7-1/2 hp at 208,240V, 10 hp at 480,600V maximum horsepower, 120V/60 Hz or 110V/50 Hz coil voltage, 27A, Five-pole, Size 1



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Freedom NEMA motor control contactor	CN15DN3AB
	<b>UPC</b>
	782113973524
<b>Product Length/Depth</b>	<b>Product Height</b>
4.44 in	5.05 in
<b>Product Width</b>	<b>Product Weight</b>
2.56 in	3.1 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year CSA Certified from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	UL Listed
	<b>Catalog Notes</b>
	Common Control

## defaultTaxonomyAttributeLabel

### HP rating - max

2 hp at 115V, 3 hp at 230V, 7-1/2 hp at 208,240V, 10 hp at 480,600V

### Phase

Single-phase, three-phase

### Amperage Rating

27A

### Size

1

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[CN15DN3\\_B 3D Model Xchange](#)

[CN15DN3\\_B 2D Drawing Xchange](#)

[CN15DN3\\_B 2D PDF](#)

[CN15DN3\\_B AutoCAD 2D Footprint \(mm\)](#)

[CN15DN3\\_B AutoCAD 2D Footprint](#)

[CN15DN3\\_B 3D Inventor](#)

### Specifications and datasheets

[Eaton Specification Sheet - CN15DN3AB](#)

[Quick Selector - NEMA Contactors](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)