

Eaton CN15GN3AB

Catalog Number: CN15GN3AB

Eaton Freedom NEMA motor control contactor, NEMA Freedom Series Non-Reversing contactor, 3 hp at 115V, 7-1/2 hp at 230V, 10 hp at 208V, 15 hp at 240V, 25 hp at 480,600V maximum horsepower, 120V/60 Hz, 45A, Four-pole, Size 2

General specifications

Product Name	Catalog Number
Eaton Freedom NEMA motor control contactor	CN15GN3AB
	UPC
	782113973555
Product Length/Depth	Product Height
4.44 in	5.05 in
Product Width	Product Weight
2.56 in	3.9 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year CSA Certified from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	UL Listed
	Catalog Notes
	Common Control



defaultTaxonomyAttributeLabel

HP rating - max

3 hp at 115V, 7-1/2 hp at 230V, 10 hp at 208V, 15 hp at 240V,
25 hp at 480,600V

Phase

Single-phase, three-phase

Amperage Rating

45A

Size

2

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[CN15GN3_B AutoCAD 2D Footprint \(mm\)](#)

[CN15GN3_B 3D Model Xchange](#)

[CN15GN3_B 2D Drawing Xchange](#)

[CN15GN3_B AutoCAD 2D Footprint](#)

[CN15GN3_B 2D PDF](#)

[CN15GN3_B 3D Inventor](#)

Specifications and datasheets

[Eaton Specification Sheet - CN15GN3AB](#)

[Quick Selector - NEMA Contactors](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)