

Eaton CN55DN3AB

Catalog Number: CN55DN3AB

Eaton Freedom NEMA motor control contactor, NEMA Freedom Series Reversing contactor, 2 hp at 115V, 3 hp at 230V, 7-1/2 hp at 208,240V, 10 hp at 480,600V maximum horsepower, 120V/60 Hz or 110V/50 Hz coil voltage, 27A, Three-pole, Size 1

General specifications



Product Name	Catalog Number
Eaton Freedom NEMA motor control contactor	CN55DN3AB
	UPC
	782113973579
Product Length/Depth	Product Height
4.44 in	5.05 in
Product Width	Product Weight
2.56 in	23 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	CSA Certified
	Catalog Notes
	Common Control

defaultTaxonomyAttributeLabel

HP rating - max

2 hp at 115V, 3 hp at 230V, 7-1/2 hp at 208,240V, 10 hp at 480,600V

Phase

Single-phase, three-phase

Amperage Rating

27A

Size

1

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[CN55DN3_B 3D Inventor](#)

[CN55DN3_B AutoCAD 2D Footprint \(mm\)](#)

[CN55DN3_B 2D Drawing Xchange](#)

[CN55DN3_B 2D PDF](#)

[CN55DN3_B 3D Model Xchange](#)

[CN55DN3_B AutoCAD 2D Footprint](#)

Specifications and datasheets

[Eaton Specification Sheet - CN55DN3AB](#)

[Quick Selector - NEMA Contactors](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)