

GND ROD CLMP, BRNZ, SIL BRZ, 1/2"-5/8"DIA, #10 SOL-#2STRND, 6MM² SOL-25MM² STRND

CATALOG NUMBER

CP58



CERTIFICATIONS









FEATURES

For use with copper-bonded ground rods

Parts that are UL 467 Listed are suitable for direct burial in earth or concrete

PRODUCT ATTRIBUTES

Material: Silicon Bronze

Ground Rod Diameter, Nominal: 1/2" - 5/8"


Ground Rod Diameter, Actual: 0.500" - 0.560"

Conductor Size: #10 Solid - #2 Stranded;6 mm² Solid - 25 mm² Stranded

Wrench Size: 1/2"

Complies With: IEC® EN 62561-1

Torque: 150 in lb



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 - Customer Care

Option 2 - Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany: 800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

