



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CR15I 15A Spec Dupl Rec B&S Wired

*Pass & Seymour/Legrand*

Catalog Number	CR15I
Manufacturer	Pass & Seymour/Legrand
Description	Straight Blade Receptacle, 15 A, 125 V, 2 Poles, 3 Wires, #14 to #10 Awg Compatible Wire Size, Wire Ground Connection, Wall Mount, 1.322 In Length, 0.78 In Width, 3.281 In Height, Thermoplastic, Ivory, Impact Resistant, Corrosion Resistant, 0.2000 LB
Weight per unit	0.1956 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	15 A
connection	Wire Ground
media	Yes
Poles	2 in
Wire Size	4 in

### Dimensions and Weight

Size	3.3 in
------	--------

### Descriptions

Description	15A SPEC DUPL REC B&S WIRED
-------------	-----------------------------

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007119060
sub brand	Pass & Seymour
UPC	785007119060

### Taxonomies, Classifications, and Categories

Category Description	Commercial recepticals
Type	Straight Blade Receptacle

### Packaging

Carton	1
Package	10
Weight Per each	0.1956

### Uses, Certifications, and Standards

Mounting	WALL
standard	UL 498



## COMMERCIAL SPEC GRADE RECEPTACLE, SIDE WIRE, 15A, 125V, IVORY

CR151 | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Commercial Spec Grade Duplex Receptacle, Side Wire 15amp 125volt, Ivory



- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- Accepts #14 - #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Ivory  
Type: Receptacles  
Special Features: Side Wire

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42  
CSA Standard: Yes  
cURus: No  
Federal Spec: No  
UL Listing No: UL498  
UL Standard: Yes

UN SPSC: 39121406

UR: No

## DIMENSIONS

Depth (US): 0.78"

Height (US): 3.281"

Width (US): 1.322"

## TECHNICAL INFORMATION

Amps: 15A

Volts: 125V

Volts (AC): 125

Capacity: Duplex

Grade Type: Commercial

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

