



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

13405 Stemmons Frwy  
75234-0000, TX Farmers Branch  
Phone: 972-206-0016  
Fax: 972-352-2818



## CR20BK Duplex Recp 20A 125V Side Wire BN

*Pass & Seymour/Legrand*

Catalog Number	CR20BK
Manufacturer	Pass & Seymour/Legrand
Description	Duplex Receptacle, 20 A, 125 V, 2 Poles, 3 Wires, #14 to #10 Awg Compatible Wire Size, Side Wire Connection, Wall Mount, 1.322 In Length, 0.78 In Width, 3.281 In Height, Thermoplastic, Black, Impact Resistant, Corrosion Resistant, 0.2000 LB
Weight per unit	0.1962 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20
connection	Wire Ground
indoor/outdoor	Indoor
Outlet Type	STRAIGHT BLADE
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	NO
Wire Size	14 - 10

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3 in
------	--------

### Descriptions

Description	DUPLEX RECP 20A 125V SIDE WIRE BN
extra long description	P&S CR20BK RECEP DUP 20A/125V SIDE

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007119107
Manufacturers Part Number	CR20BK
UPC	785007119107

### Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Outlet

### Trade Size

Amperage	20.0
----------	------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

13405 Stemmons Frwy  
75234-0000, TX Farmers Branch  
Phone: 972-206-0016  
Fax: 972-352-2818

## Packaging

Carton	1
Package	100
Weight Per each	0.1962

## Uses, Certifications, and Standards

Mounting	WALL
Operating Temperature standard	-40°-60°C CULUS, UL 498