



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CRB5362I 20A 125V Construct Duplex Recp Iv

*Pass & Seymour/Legrand*

Catalog Number	CRB5362I
Manufacturer	Pass & Seymour/Legrand
Description	Duplex Receptacle, 20 A, 125 V, 2 Poles, 3 Wires, #14 to #10 Awg Compatible Wire Size, Back and Side Wired Connection, Wall Mount, 3.3 In Length, Thermoplastic, Ivory, Corrosion Resistant; Impact Resistant, 0.2000 LB
Weight per unit	0.2050 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20
connection	Wire Ground
indoor/outdoor	Indoor
Outlet Type	STRAIGHT BLADE
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	NO
Wire Size	14 - 10

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3 in
------	--------

### Descriptions

Description	20A 125V CONSTRUCT DUPLEX RECP IV
extra long description	P&S CRB5362I 20A 125V CONSTRUCT DUP

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007210224
Manufacturers Part Number	CRB5362I
UPC	785007210224

### Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Outlet

### Trade Size

Amperage	20.0
----------	------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	100
Weight Per each	0.205

## Uses, Certifications, and Standards

Mounting	WALL
Operating Temperature	-40°-60°C
standard	FEDSPEC, CULUS, UL 498, FEDSPEC