



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4281 Crawford Dr.
79602, TX Abilene
Phone: 325-793-1570
Fax: 325-692-9649



CRB5362W 20A 125V Construct Duplex Recp WH

Pass & Seymour/Legrand

Catalog Number	CRB5362W
Manufacturer	Pass & Seymour/Legrand
Description	Duplex Receptacle, 20 A, 125 V, 2 Poles, 3 Wires, #14 to #10 Awg Compatible Wire Size, Back and Side Wired Connection, Wall Mount, 1.322 In Length, 0.78 In Width, 3.281 In Height, Thermoplastic, White, Corrosion Resistant; Impact Resistant, 0.2100 LB
Weight per unit	0.2050 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Wire Ground
indoor/outdoor	Indoor
Outlet Type	STRAIGHT BLADE
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	NO
Wire Size	14 - 10

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	20A 125V CONSTRUCT DUPLEX RECP WH
extra long description	P&S CRB5362W 20A 125V CONSTRUCT DUP

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007210231
Manufacturers Part Number	CRB5362W
UPC	785007210231

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Outlet

Trade Size

Amperage	20.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4281 Crawford Dr.
79602, TX Abilene
Phone: 325-793-1570
Fax: 325-692-9649

Packaging

Carton	1
Package	100
Weight Per each	0.205

Uses, Certifications, and Standards

Mounting	WALL
Operating Temperature	-40°-60°C
standard	FEDSPEC, CULUS, UL 498, FEDSPEC