

Specifications



Eaton CS115GY

Eaton commercial grade toggle switch, #14-10 AWG, 15A, Commercial, Flush, 120/277V, Side wire, Screw, Gray, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Fluorescent, Halogen, Single-Pole, Single-Pole, Brass, PVC

General specifications

PRODUCT NAME	Eaton commercial grade toggle switch
CATALOG NUMBER	CS115GY
UPC	032664487484
PRODUCT LENGTH/DEPTH	1.3 in
PRODUCT HEIGHT	4.2 in
PRODUCT WIDTH	0.902 in
PRODUCT WEIGHT	0.11 lb
CERTIFICATIONS	cULus Listed NOM Federal Specification Classification 6241 05
PRODUCT TYPE	Commercial grade toggle switch

Product specifications

TYPE	Toggle switch
AMPERAGE RATING	15A
VOLTAGE RATING	120/277 V
NUMBER OF POLES	Single-pole
APPLICATION	Commercial
WIRING METHOD	Side wire
SWITCH TYPE	Single-pole
MOUNTING METHOD	Flush
CONNECTOR TYPE	Screw
LOAD TYPE	HAL INC CFL FLR LED ELV MLV Fan Motor Control
MATERIAL	PVC
ALLOWABLE WIRE SIZE	#14-10 AWG
TERMINAL ENCLOSURE MATERIAL	Brass
COLOR	Gray

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - CS115GY](#)

[Commercial specification grade switches spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

