



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CS15AC3W 15A 3W Spec Switch 120/277V

Pass & Seymour/Legrand

Catalog Number	CS15AC3W
Manufacturer	Pass & Seymour/Legrand
Description	Commercial Switch, 3 Poles, 3 Ways, 15 A, 120/277 V Ac, Nylon Material, Silver Cadmium Oxide Contact Material, White, Grounding Connection, Toggle Actuator, Wall Mount, 1.320 (L) X 1.073 (W) X 3.281 (H) In, -40 °C Operating Temperature, +115 °C Operating Temperature, 0.18 LB
Weight per unit	0.1804 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	TP
actuator	Toggle
amperage rating	15 A
Contact Rating	20Amp, 120/277V
insulation	None IN
Poles	3 in

Dimensions and Weight

Size	3.3"
------	------

Descriptions

Description	15A 3W SPEC SWITCH 120/277V
-------------	-----------------------------

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007126518
sub brand	Pass & Seymour
UPC	785007126518

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	SWITCH

Packaging

Carton	10
Package	50
Weight Per each	0.1804

Uses, Certifications, and Standards

Mounting	WALL
standard	UL20



COMMERCIAL SPECIFICATION GRADE SWITCH, WHITE

CS15AC3W | [Pass & Seymour](#)

FEATURES & BENEFITS

Commercial 3way Switch, Side Wire, 15amp 120/277volt, White.



- One-piece brass alloy contact arm for reliable electrical performance.
- One-piece steel strap with integral ground is plated for corrosion resistance.
- High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.
- Heavy-duty toggle bumpers for smooth and quiet operation.
- Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.
- Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.
- Cam designed for fast make with positive break action to minimize arcing and prolong switch life.
- Oversized silver alloy contacts for longer dependable switch life.
- Tri-drive terminal and mounting screws.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: White
Type: Side Wire
Duty: Heavy Duty
Number Of Poles: 3-way

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: C22.2 111
CSA Standard: Yes

Federal Spec: Yes
UL Listing No: 20
UL Standard: Yes
UN SPSC: 39121507

DIMENSIONS

Depth (US): 1.073"
Height (US): 3.281"
Width (US): 1.320"

TECHNICAL INFORMATION

Amps: 15A
Volts: 120/277VAC
Volts (AC): 120/277
Grade Type: Commercial

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

