



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CS15AC3W 15A 120/277VAC S Wire Comm 3W SW WH *Pass & Seymour/Legrand*

Catalog Number	CS15AC3W
Manufacturer	Pass & Seymour/Legrand
Description	Commercial Switch, 3 Poles, 3 Ways, 15 A, 120/277 V Ac, Nylon Material, Silver Cadmium Oxide Contact Material, White, Grounding Connection, Toggle Actuator, Wall Mount, 1.320 (L) X 1.073 (W) X 3.281 (H) In, -40 °C Operating Temperature, +115 °C Operating Temperature, 0.18 LB
Weight per unit	0.1804 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	TP
actuator	Toggle
amperage rating	15
Contact Rating	15amp, 120/277vac
indoor/outdoor	Indoor
insulation	False
Load Rating	15 A @ 120/277 VAC
Load Type	Xenon, LED, Incandescent, Universal, Fluorescent, Halogen, CFL
media	Yes
Number of Gangs	1
Number of Switches	1.0
Poles	3-way
Switch Type	Toggle
throw type	Double Throw
Voltage	120 VAC, 277 VAC
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3"
------	------

Descriptions

Description	15A 120/277VAC S WIRE COMM 3W SW W
extra long description	P&S CS15AC3W 15A 120/277VAC S WIRE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007126518
Manufacturers Part Number	CS15AC3W
UPC	785007126518

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	SWITCH

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.1804

Uses, Certifications, and Standards

Mounting	WALL
standard	FEDSPEC, CULUS, UL20, FEDSPEC