



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CS20AC1LA 20A 120/277VAC S Wire Comm SP SW La

*Pass & Seymour/Legrand*

Catalog Number	CS20AC1LA
Manufacturer	Pass & Seymour/Legrand
Description	Toggle Switch, 1 Pole, 20 A, 120/277 V Ac, Nylon Material, Silver Cadmium Oxide Contact Material, Light Almond, Grounding Connection, Wall Mount, 1.320 (L) X 1.073 (W) X 3.281 (H) In, -40 °C Operating Temperature, +115 °C Operating Temperature, 0.16 LB
Weight per unit	0.1640 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	Single pole
actuator	Toggle
amperage rating	20
Contact Rating	20Amp, 120/277Vac
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	Halogen, Universal, Xenon, LED, Fluorescent, CFL, Incandescent
Number of Gangs	1
Number of Switches	1.0
Poles	1
Switch Type	Toggle
throw type	Single Throw
Voltage	120 VAC, 277 VAC
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3 in
------	--------

### Descriptions

Description	20A 120/277VAC S WIRE COMM SP SW LA
extra long description	P&S CS20AC1LA 20A 120/277VAC S WIRE

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007126464
Manufacturers Part Number	CS20AC1LA
UPC	785007126464



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	SWITCH

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	50
Weight Per each	0.164

## Uses, Certifications, and Standards

Application	Commercial
Enclosure	Nylon
Mounting	WALL
standard	FEDSPEC, CULUS, UL 498/20, FEDSPEC