



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CS20AC3 20A 3W Comm SW

*Pass & Seymour/Legrand*

Catalog Number	CS20AC3
Manufacturer	Pass & Seymour/Legrand
Description	
Weight per unit	0.1820 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	SP
actuator	Toggle
amperage rating	20 A
Contact Rating	15Amp, 120/277V
insulation	None IN
media	Yes
Poles	3 in
Voltage Rating	120/277 VAC

### Material, Color, and Finish

Color	BROWN
-------	-------

### Dimensions and Weight

Size	3.3"
------	------

### Descriptions

Description	20A 3W COMM SW
Product Type	20A 120/277VAC S Wire Comm 3W SW
Special Features	Back & Side wire, locking support, one piece brass alloy contact arm

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007126525
Manufacturers Part Number	CS20AC3
sub brand	Pass & Seymour
UPC	785007126525

### Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	SWITCH

### Packaging

Carton	1
Package	10
Weight Per each	0.182



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	COMMERCIAL/RESIDENTIAL
Mounting	WALL
standard	UL20



## COMMERCIAL SPECIFICATION GRADE SWITCH, BROWN

CS20AC3 | [Pass & Seymour](#)

### FEATURES & BENEFITS

Commercial 3way Switch, Side Wire, 20amp 120/277volt, Brown.



- One-piece brass alloy contact arm for reliable electrical performance.
- One-piece steel strap with integral ground is plated for corrosion resistance.
- High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.
- Heavy-duty toggle bumpers for smooth and quiet operation.
- Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.
- Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.
- Cam designed for fast make with positive break action to minimize arcing and prolong switch life.
- Oversized silver alloy contacts for longer dependable switch life.
- Tri-drive terminal and mounting screws.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Brown  
Type: Side Wire  
Duty: Heavy Duty  
Number Of Poles: 3-way

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 111  
CSA Standard: Yes  
Federal Spec: Yes

UL Listing No: 20  
UL Standard: Yes  
UN SPSC: 39121507

#### **DIMENSIONS**

Depth (US): 1.073"  
Height (US): 3.281"  
Width (US): 1.320"

#### **TECHNICAL INFORMATION**

Amps: 20A  
Volts: 120/277VAC  
Volts (AC): 120/277  
Grade Type: Commercial

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

