



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5510 West 65th Street
72209-0000, AR Little Rock
Phone: 501-565-1785
Fax: 501-565-0827



CS20AC3GRY 20A 120/277VAC S Wire Comm 3W SW Gy

Pass & Seymour/Legrand

Catalog Number	CS20AC3GRY
Manufacturer	Pass & Seymour/Legrand
Description	Toggle Switch, 3 Poles, 3 Ways, 20 A, 120/277 V Ac, Nylon Material, Silver Cadmium Oxide Contact Material, Gray, Grounding Connection, Wall Mount, 1.320 (L) X 1.073 (W) X 3.281 (H) In, -40 °C Operating Temperature, +115 °C Operating Temperature, 0.18 LB
Weight per unit	0.1820 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	Three pole
actuator	Toggle
amperage rating	20
connection	locking support, one piece brass alloy contact arm, Back & Side wire
Contact Configuration	One piece brass alloy contact arm
Contact Rating	Oversized silver alloy contacts
Degree of Protection	1500V Dielectric Withstand Voltage
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	Incandescent, Halogen, CFL, Fluorescent, Universal, Xenon, LED
media	Yes
Number of Gangs	1
Number of Switches	1.0
Poles	3-way
Switch Type	Toggle
throw type	Double Throw
Voltage	120 VAC, 277 VAC
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	20A 120/277VAC S WIRE COMM 3W SW GY
extra long description	P&S CS20AC3GRY 20A 120/277VAC S WIR



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5510 West 65th Street
72209-0000, AR Little Rock
Phone: 501-565-1785
Fax: 501-565-0827

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007126594
Manufacturers Part Number	CS20AC3GRY
UPC	785007126594

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	SWITCH

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.182

Uses, Certifications, and Standards

Application	Commercial
Enclosure	Nylon
Mounting standard	WALL FEDSPEC, CULUS, UL Listed E140597, Standard UL20, FedSpec WS896, Flammability Rating UL94 V2, FEDSPEC