Twist-Lock® Devices 50A, 125/250V AC, 3 Pole, 4 Wire Grounding Flanged Inlet

HUBBELL

Features

- Metallic flanged casing provides maximum strength and protection
- Thermoset interior provides superior heat resistance

Ordering Information

Description Zinc plated steel casing, thermoset interior

Device Style Metallic

UPC Catalog Number 783585828206 CS6375

Listings

Listed to UL 498 Certified to CSA C22.2 No.42

Specifications

Steel, zinc plated Terminal Retainer Phenolic Blades **Brass Terminal Screws** Steel

Performance

Electrical

Certified for current interrupting at full rated current **Current Interrupting** Dielectric Voltage Withstands 2,000V minimum

Mechanical


Terminal Accommodation #10 AWG - #6 AWG solid or stranded copper wire only

Environmental

Flammability UL 94 V0

Maximum continuous 75°C; minimum -40°C (w/o impact) **Operating Temperatures**





Accessories

Connector CS6364C

Resources

Customer Use Drawing eCatalog

