

Eaton CS8164

Catalog Number: CS8164

Eaton locking connector, #10-6 AWG, 50A, Industrial, 480V, Back wiring, Steel, Armored, Non-NEMA, Three-pole, Four-wire, Steel, 0.68 to 1.13 in, California standard

General specifications

Product Name	Catalog Number
Eaton Arrow Hart armored California standard locking connector	CS8164
	UPC
	040893681627
Product Length/Depth	Product Height
5.73 in	2.68 in
Product Width	Product Weight
3.1 in	1.2 lb
Warranty	Certifications
Refer to warranty document.	CSA certified
	cULus Listed



Product specifications

Special features

Armored

Color

Steel

Face/body material

Glass filled nylon

Wiring method

Back

Material

Stainless steel

Standard

California standard

Allowable wire size

#10-6 AWG

Amperage Rating

50 A

Number Of Poles

Three-pole

Contact material

Zinc plated brass

Type

Locking connector

Device grade

Extra heavy duty

NEMA configuration

Non-NEMA

Design type

Armored

Number of wires

4

Grounding

Operating temperature

-40 to 90 °C (-40 to 194 °F)

Voltage rating

3Ø 480 V

Resources

Catalogs

[Arrow Hart Buyers Guide Section C](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - CS8164](#)

Cord diameter

0.68-1.13 in (17.3-28.6 mm)

Application

Industrial

Torque rating

25 lbf-inch



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia