



CS6365C Plug & CS6364C Connector

## Safe and Durable 50A Power Connections

Our 50A Turnlok Plugs and Connectors make installing and securing your connections faster, safer and more dependable than ever. These devices are designed to withstand harsh environments. 50A Turnlok Plugs and Connectors feature a simple push, twist and lock body assembly for greater productivity and labor savings in temporary power applications. The back body easily slides onto the device and locks in place with a quarter twist making installations faster, safer and more dependable.

## Features & Benefits

### Feature:

- Quality Materials, durability, and time-tested design.
- Push, twist and lock design that eliminates the need for time-consuming threading
- Industrial-Strength Brass Alloy Plug Blades and Connector Contacts: Resist heat rise and provide excellent conductivity.
- Nylon 66 shell material is impact and UV-resistant
- Features an adjustable cord clamp strategically located outside the back body to accommodate various cord sizes
- Device's same-plane hex terminations make every termination faster and safer
- Integral flexible rubber cord grommet provides protection from oils, water or chips entering the wiring chamber

## Vertical Markets

- Construction Sites
- Entertainment Venues
- Data Center
- Outdoor Events
- Disaster Relief

## Compliance

 cULus Listed Wiring Assembly: File E146159.  
Standard UL498 Attachment Plugs and Receptacles

---

## Technical Information

### Performance

---

#### Electrical

Dielectric Withstand Voltage	Withstands 3000V
Number of Wires	3/4
Number of Poles	2/3
Frequency	60 Hz
Voltage Range	125-600V

---

#### Mechanical

Terminal Identification	"GR" and Green color = Ground, "WH" and White color = Neutral, "X", "Y", "Z" = Hot
Terminal Accommodation	#8 AWG min. - #4 AWG max.
Product Identification	Amperage, Voltage, 3rd Party Compliance, hot stamped onto device

---

#### Environmental

Operating Temperature	Maximum continuous +75°C, minimum -40°C without impact
Maximum Humidity	95%
Flammability	UL94 V2

---

#### Material Specs

Face	Nylon 66
Body	Nylon 66
Contacts	.05" Brass
Mounting Strap	Galvanized Steel
Terminal Screws	Nickel-Plated Steel #5/16 - 24


---

## Warranty

1 Year

## Ordering Information

Catalog No./Item	Ratings		Description/Color	Cord Diameter
	A.	V.		
<b>Connectors California Standard</b>				
CS6360C	50A	125V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
CS6364C	50A	125/250V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
CS8164C	50A	3ø480V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
CS8264C	50A	250V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
CS8364C	50A	3ø250V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
CS8464C	50A	480V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
<b>Plugs California Standard</b>				
CS6361C	50A	125V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
CS6365C	50A	125/250V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
CS8165C	50A	3ø480V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
CS8265C	50A	250V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
CS8365C	50A	3ø250V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
CS8465C	50A	480V	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
<b>Connectors Corrosion Resistant</b>				
CR6360C	50A	125V	Yellow Back, White Front Body	.700"-1.200" 8AWG-4AWG
CR6364C	50A	125/250V	Yellow Back, White Front Body	.700"-1.200" 8AWG-4AWG
<b>Plugs Corrosion Resistant</b>				
CR6361C	50A	125V	Yellow Back, White Front Body	.700"-1.200" 8AWG-4AWG
CR6365C	50A	125/250V	Yellow Back, White Front Body	.700"-1.200" 8AWG-4AWG
<b>Connectors 50A Turnlok</b>				
3762C	50A	600VAC/250VAC	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
3764C	50A	600VAC/250VDC	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
7764C	50A	600VAC/250VDC	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
<b>Plugs 50A Turnlok</b>				
3763MC	50A	600VAC/250VAC	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
3765C	50A	600VAC/250VDC	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG
7765C	50A	600VAC/250VDC	Black Back, White Front Body	.700"-1.200" 8AWG-4AWG



---

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



**Legrand, North America**  
60 Woodlawn Street  
West Hartford, CT 06110  
877-295-3472  
[www.legrand.us](http://www.legrand.us)

**Canada**  
844-977-3783  
[www.legrand.ca](http://www.legrand.ca)

FOLLOW US

