Eaton CS8169

Catalog Number: CS8169

Eaton locking receptacle, #10-6 AWG, 50A, Industrial, 480V, Back wiring, Black, Single, Non-NEMA, Three-pole, Four-wire, Nylon, California standard

General specifications



Product Name Catalog Number

Eaton Arrow Hart California standard CS8169

locking receptacle

UPC

040893679686

Product Length/Depth Product Height

6.25 in 3.25 in

Product Width Product Weight

3 in 0.88 lb

Warranty

Refer to warranty document.

Certifications
UL Listed

CSA certified

cULus Listed



Product specifications

Special features

Locking plug

Color

Black

Face/body material

Glass filled nylon

Wiring method

Back

Material

Steel

Standard

California standard

Allowable wire size

#10-6 AWG

Amperage Rating

50 A

Number Of Poles

Three-pole

Contact material

Zinc plated brass

Туре

Locking receptacle

Device grade

Extra heavy duty

NEMA configuration

Non-NEMA

Design type

Single receptacle

Number of wires

4

Grounding

Operating temperature

-40 to 105 °C (-40 to 221 °F)

Receptacle type

Locking

Resources

Catalogs

Arrow Hart Buyers Guide Section C

Multimedia

Arrow Hart - Connecting Safety to Reliability since 1890

Specifications and datasheets

Eaton Specification Sheet - CS8169

Voltage rating

3Ø 480 V

Application

Industrial

Torque rating

45 lbf-inch



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia