

Eaton CS8265EX

Catalog Number: CS8265EX

Eaton locking plug, #10-6 AWG, 50A, Industrial, 250V, Back wiring, Black, red, Non-NEMA, Two-pole, Three-wire, Nylon, 0.44 to 1.06 in, California standard

General specifications



Product Name

Eaton Arrow Hart pro grip California standard locking plug

Catalog Number

CS8265EX

UPC

032664663925

Product Length/Depth

6.94 in

Product Height

3.38 in

Product Width

3.61 in

Product Weight

1.05 lb

Warranty

Refer to warranty document.

Compliances

RoHS Compliant

Certifications

cULus Listed

CSA certified



Powering Business Worldwide

Product specifications

Special features

Locking plug

Color

Red

Black

Face/body material

Glass filled nylon

Wiring method

Back

Material

Nylon

Standard

California standard

Allowable wire size

#10-4 AWG

Amperage Rating

50 A

Number Of Poles

Two-pole

Contact material

Zinc plated brass

Type

Locking plug

Device grade

Extra heavy duty

NEMA configuration

Non-NEMA

Design type

Pro grip

Number of wires

Grounding

3

Operating temperature

-40 to 105 °C (-40 to 221 °F)

Voltage rating

250 V

Resources

Catalogs

[Arrow Hart Buyers Guide Section C](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - CS8265EX](#)

Cord diameter

0.44-1.06 in (11.1-26.0 mm)

Application

Industrial

Torque rating

45 lbf-inch



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia