Twist-Lock® Devices 50A, 250V AC, 2 Pole, 3 Wire Grounding Receptacle

HUBBELL

Features

- Thermoset construction offers high heat resistance
- Armored housing provides superior impact resistance
- One piece contacts provide low operating temperatures

Ordering Information

Description	Device Color	UPC	Catalog Number
Phenolic	Black	783585828909	CS8269

Listings

Listed to UL 498 Certified to CSA C22.2 No.42

Specifications

Body	Phenolic	
Face	Phenolic	
Contacts	Brass	
Terminal Screws	Steel	
Insulator	Phenolic	

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical


Terminal Accommodation #10 AWG - #4 AWG solid or stranded copper wire only

Environmental

Flammability UL 94 V0

Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)





Accessories

Plug CS8265C
Weatherproof Lift Cover HBL7774WO
Single Gang Stainless Steel Wallplate
4" Square Raised Cover HBL50SC

Resources

Customer Use Drawing eCatalog

