

# Eaton CSAS4F4CY2205

Catalog Number: CSAS4F4CY2205

Eaton Photoelectric Sensor Connector Cable, Global Plus, Accessory, Sensor connectivity, Micro-style straight female, AC, 4-wire, 22 AWG, 16.4 ft, 4 pin, PVC, 320V

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Global Plus connector cable	CSAS4F4CY2205
<b>UPC</b>	<b>Product Length/Depth</b>
782116056965	196.8 in
<b>Product Height</b>	<b>Product Width</b>
0.58 in	0.58 in
<b>Product Weight</b>	<b>Warranty</b>
0.6 lb	1 year
<b>Certifications</b>	
UL Listed	
CSA Certified	

**Type**

Accessory

**Cord length**

196.8 ft

**Operating Temperature**

-13° to 176°F (-25° to 80°C)

**Cable type**

Polyvinyl Chloride (PVC)

**Connection**

Micro-style straight female

**Number of wires**

4

**Wire size**

#22 AWG

**Environmental rating**

IP67

**Input voltage**

320 V

**Series**

Global Plus

**Switch type**

Sensor connectivity

**Power consumption**

AC

**Number of pins**

4

**Catalogs**

[Volume 6: Solid-State Motor Control](#)

[Eaton's Volume 8—Sensing Solutions](#)

**Specifications and datasheets**

[Eaton Specification Sheet - CSAS4F4CY2205](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)