

# Specifications



## Eaton CSB120V

Eaton commercial grade toggle switch, #14-10 AWG, 20A, Commercial, Flush, 120/277V, Back and side, Screw, Ivory, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Flourescent, Halogen, Single-Pole, Single-Pole, Brass, PVC

### General specifications

<b>PRODUCT NAME</b>	Eaton commercial grade toggle switch
<b>CATALOG NUMBER</b>	CSB120V
<b>UPC</b>	032664559051
<b>PRODUCT LENGTH/DEPTH</b>	1.3 in
<b>PRODUCT HEIGHT</b>	4.2 in
<b>PRODUCT WIDTH</b>	0.902 in
<b>PRODUCT WEIGHT</b>	0.2 lb
<b>CERTIFICATIONS</b>	cULus Listed NOM Federal Specification Classification 6241 05
<b>PRODUCT TYPE</b>	Commercial grade toggle switch



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Toggle switch
<b>AMPERAGE RATING</b>	20A
<b>VOLTAGE RATING</b>	120/277 V
<b>NUMBER OF POLES</b>	Single-pole
<b>APPLICATION</b>	Commercial
<b>WIRING METHOD</b>	Back and side
<b>SWITCH TYPE</b>	Single-pole
<b>MOUNTING METHOD</b>	Flush
<b>CONNECTOR TYPE</b>	Screw
<b>LOAD TYPE</b>	ELV INC MLV Motor Control FLR Fan HAL LED CFL
<b>MATERIAL</b>	PVC
<b>ALLOWABLE WIRE SIZE</b>	#14-10 AWG
<b>TORQUE RATING</b>	14 lbf-inch
<b>TERMINAL ENCLOSURE MATERIAL</b>	Brass
<b>TERMINALS</b>	0.031 in
<b>COLOR</b>	Ivory

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - CSB120V</a>
	<a href="#">Commercial specification grade switches spec sheet</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

