



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

6 South Hickory
71373-0000, LA Vidalia
Phone: 318-336-5113
Fax: 318-336-5587



CSD302410SS 60X24X10 N4X SS4 HC, QTR TRN LTCH

Hoffman Enclosures, Inc.

Catalog Number	CSD302410SS
Manufacturer	Hoffman Enclosures, Inc.
Description	Concept Wallmount 1/4-Turn Latch Type 4X, 30X24X10, Brushed, Stainless 304
Weight per unit	53.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

ip rating	IP66
Latch Type	Quarter-Turn
Material	Stainless Steel;Stainless Steel 304

Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4
Style	Quarter-turn

Dimensions and Weight

Depth	10
Height	30
Size	30.00x24.00x10.00 in
Width	24

Descriptions

Description	60X24X10 N4X SS4 HC, QTR TRN LTCH
extra long description	NVENT HOF CSD302410SS Wall Mount Ty
Features	For indoor or outdoor applications that require corrosion protection from chemicals and water. Concept Enclosures feature streamlined styling with an attractive stroked finish and flush quarter-turn latches for secure closure.
Long Description	Concept Wallmount 1/4-Turn Latch Type 4X, 30x24x10, Brushed, Stainless 304
Product Type	Wall Mount Type 4X Enclosure
Short Description	Wall Mount Type 4X Enclosure

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510128685
Manufacturers Part Number	CSD302410SS
UPC	783510128685



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

6 South Hickory
71373-0000, LA Vidalia
Phone: 318-336-5113
Fax: 318-336-5587

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Wall Mounted Industrial Enclosures

Packaging

Carton	1
Weight Per each	53

Uses, Certifications, and Standards

Application	Controls and Drives;Corrosive Environments
nema rating	4X