



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

12555 Harris Branch Pkwy Suite 105
78653-0000, TX Manor
Phone: 512-339-8750
Fax: 512-339-6732



CSD302412SS 30X24X12 N4X SS4 HC QTR TRN LTCH

Hoffman Enclosures, Inc.

Catalog Number	CSD302412SS
Manufacturer	Hoffman Enclosures, Inc.
Description	Concept Wallmount 1/4-Turn Latch Type 4X, 30X24X12, Brushed, Stainless 304
Weight per unit	49.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

ip rating	IP66
Latch Type	Quarter-Turn
Material	Stainless Steel;Stainless Steel 304

Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4
Style	Quarter-turn

Dimensions and Weight

Depth	12
Height	30
Size	30.00x24.00x12.00 in
Width	24

Descriptions

Description	30X24X12 N4X SS4 HC QTR TRN LTCH
extra long description	NVENT HOF CSD302412SS Stainless Enc
Features	For indoor or outdoor applications that require corrosion protection from chemicals and water. Concept Enclosures feature streamlined styling with an attractive stroked finish and flush quarter-turn latches for secure closure.
Long Description	Concept Wallmount 1/4-Turn Latch Type 4X, 30x24x12, Brushed, Stainless 304
Product Type	Stainless Encl. 30.00X24.00X12
Short Description	Stainless Encl. 30.00x24.00x12

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510488406
Manufacturers Part Number	CSD302412SS
UPC	783510488406



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

12555 Harris Branch Pkwy Suite 105
78653-0000, TX Manor
Phone: 512-339-8750
Fax: 512-339-6732

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Wall Mounted Industrial Enclosures

Packaging

Carton	1
Weight Per each	49

Uses, Certifications, and Standards

Application	Controls and Drives;Corrosive Environments
nema rating	4X