



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **CSD30248WSS 30X24X8 N4X WNDW HC** *Hoffman Enclosures, Inc.*

Catalog Number	CSD30248WSS
Manufacturer	Hoffman Enclosures, Inc.
Description	Concept Window Door 1/4 Turn Latch Type 4X, 30X24X8, Brushed, Stainless 304
Weight per unit	44.3 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

### **Features**

ip rating	IP66
Material	Stainless Steel 304

### **Material, Color, and Finish**

Color	Unpainted
Finish	Brushed #4
Style	Quarter-turn

### **Dimensions and Weight**

Depth	8
Height	30
Size	30.00x24.00x8.00 in
Width	24

### **Descriptions**

Description	30X24X8 N4X WNDW HC
extra long description	NVENT HOF CSD30248WSS 30.00x24.00x8
Features	For indoor or outdoor applications that require corrosion protection from chemicals and water. Concept Enclosures feature streamlined styling with an attractive stroked finish and flush quarter-turn latches for secure closure.
Long Description	Concept Window Door 1/4 Turn Latch Type 4X, 30x24X8, Brushed, Stainless 304
Product Type	30.00X24.00X8.00

### **Manufacturer Information**

Brand	Nvent Hoffman
GTIN	00783510117900
Manufacturers Part Number	CSD30248WSS
UPC	783510117900

### **Taxonomies, Classifications, and Categories**

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Wall Mounted Industrial Enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	44.2999

## Uses, Certifications, and Standards

Application	Corrosive Environments, Controls and Drives
nema rating	4X Watertight, corrosion-resistant