

Eaton CSDS4A4CY2205

Catalog Number: CSDS4A4CY2205

Eaton Photoelectric Sensor Connector Cable, Global Plus, Accessory, Sensor connectivity, Micro-style straight female, DC, 4-wire, 22 AWG, 16.4 ft, 4 pin, PVC, 320V

General specifications



| | |
|-----------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton Global Plus connector cable | CSDS4A4CY2205 |
| UPC | Product Length/Depth |
| 782116056828 | 196.8 in |
| Product Height | Product Width |
| 0.58 in | 0.58 in |
| Product Weight | Warranty |
| 0.9 lb | 1 year |
| Certifications | |
| UL Listed | |
| CSA Certified | |

Type

Accessory

Cord length

196.8 ft

Operating Temperature

-13° to 176°F (-25° to 80°C)

Cable type

Polyvinyl Chloride (PVC)

Connection

Micro-style straight female

Number of wires

4

Wire size

#22 AWG

Environmental rating

IP67

Input voltage

320 V

Series

Global Plus

Switch type

Sensor connectivity

Power consumption

DC

Number of pins

4

Catalogs

Eaton's Volume 8—Sensing Solutions

Volume 6: Solid-State Motor Control

Specifications and datasheets

Eaton Specification Sheet - CSDS4A4CY2205



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)