

Eaton CSH2125N

Catalog Number: CSH2125N

Eaton Type CSH Main Circuit Breaker, Main circuit breaker, 125 A, 35 kAIC, Two-pole, 120/240 V, CH, #2 AWG-300 kcmil Cu/Al, CSH, CH24NLPN125E, CH32NLPN225J, CH42NLPN225K, type ECB unit enclosures

General specifications



Product Name	Eaton CSH main breaker	Catalog Number	CSH2125N
UPC	786685229126	Product Length/Depth	1 in
Product Height	1 in	Product Width	1 in
Product Weight	1 lb	Warranty	Limited lifetime residential, 1 year commercial
Certifications	UL Listed	Catalog Notes	For use in Type ECB Unit Enclosures

defaultTaxonomyAttributeLabel

Type

Main circuit breaker

Amperage Rating

125 A

Voltage rating

120/240 V

Circuit breaker frame type

CSH

Used with

CH24NLPN125E, CH32NLPN225J, CH42NLPN225K, type ECB
unit enclosures

Interrupt rating

35 kAIC

Main circuit breaker

CH

Wire size

#2 AWG-300 kcmil Cu/Al

Number of poles

Two-pole

Resources

Brochures

[Plug-on Neutral Loadcenter](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CSH2125N](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia