

Eaton CSH2225N

Catalog Number: CSH2225N

Eaton Type CSH Main Circuit Breaker, Main circuit breaker, 225 A, 35 kAIC, Two-pole, 120/240 V, CH, #2 AWG-300 kcmil Cu/Al, CSH, Type ECB unit enclosures

General specifications

Product Name	Catalog Number
Eaton CSH main breaker	CSH2225N
UPC	Product Length/Depth
782113099774	1 in
Product Height	Product Width
1 in	1 in
Product Weight	Warranty
1 lb	Limited lifetime residential, 1 year commercial
Certifications	Catalog Notes
UL Listed	For use in Type ECB Unit Enclosures



Product specifications

Interrupt rating

35 kAIC

Type

Main circuit breaker

Wire size

#2 AWG-300 kcmil Cu/Al

Used with

Type ECB Unit Enclosures

Main circuit breaker

CH

Circuit breaker frame type

CSH

Voltage rating

120/240 V

Amperage Rating

225 A

Number of poles

Two-pole

Resources

Brochures

[Plug-on Neutral Loadcenter](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CSH2225N](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)