

**DESCRIPTION**

The CSL LED striplight brings together an economical price point and high performance available in 4ft and 8ft lengths.



tradeSELECT™



**FEATURES**

- 4,000 and 8,000 nominal lumens
- 54,000 hour LEDs at L70 for reduced maintenance
- Up to 112 lumens per watt
- Choice of two color temperatures
- 0-10V dimming, standard
- Fully assembled for quick installation
- Frosted acrylic lens
- Wide range of applications
- Surface mount on wall or ceiling
- Universal voltage (120-277V)
- 80+ CRI
- DesignLights Consortium® (DLC) qualified; see [www.designlights.org](http://www.designlights.org)

**STANDARDS, CERTIFICATION AND COMPLIANCE**

All luminaires are built to UL1598 standards and bear appropriate UL labels. Damp location label standard. DesignLights Consortium® (DLC) qualified. Please refer to the DLC website for specific product qualifications at [www.designlights.org](http://www.designlights.org).


**WARRANTY**

Five year warranty. Terms and conditions apply.


**ORDERING GUIDE**

Catalog Number	Description	Lumens	Watts	LPW	Qty on Pallet
<b>CSL4-4035</b>	4ft LED Striplight, 4,000 Lumens, 3500K, 0-10V dimming	4231	40.2	105	120
<b>CSL4-4040</b>	4ft LED Striplight, 4,000 Lumens, 4000K, 0-10V dimming	4517	40.2	112	120
<b>CSL8-8035</b>	8ft LED Striplight, 8,000 Lumens, 3500K, 0-10V dimming	8460	80.5	105	120
<b>CSL8-8040</b>	8ft LED Striplight, 8,000 Lumens, 4000K, 0-10V dimming	9036	80.5	112	120

**DIMENSIONS**




A - 7/8" Diameter Knockout  
B - 5/32" x 1/4" Hole




**Accessories (Order Separately)**

- GLH5** 5' adjustable cable for suspension mount



A - 7/8" Diameter Knockout  
B - 5/32" x 1/4" Hole



**PHOTOMETRIC DATA**

Test #17614 Test Date 2/15/2017

**LUMINAIRE DATA**

Luminaire	CSL4-4035 tradeSELECT® CSL, Striplight 48" x 2.25" LED striplight with opal lens
Ballast	SL38-1900
Ballast Factor	1.00
Lamp	LED
Fixture Lumens	4231
Watts	40.24
Mounting	Recessed
Shielding Angle	0° = 90 90° = 90
Spacing Criterion	0° = 1.25 90° = 1.26
Luminous Opening in Feet	Length: 4.00 Width: 0.17 Height: 0.08


**ZONAL LUMEN SUMMARY**

Zone	Lumens	% Lamp	% Fixt.
0-30	935	22.1	22.1
0-40	1536	36.3	36.3
0-60	2768	65.4	65.4
0-90	3902	92.2	92.2
0-180	4231	100.0	100.0

**ENERGY DATA**

Total Luminaire Efficiency	100.0%
Total Lumens per Watt	105
IESNA RP-1-2004 Compliance	Non-Compliant
Comparative Yearly Lighting Energy Cost per 1000 Lumens	\$2.26 based on 3000 hrs. and \$0.08 per KWH

**INDOOR CANDELA PLOT**



**PHOTOMETRIC DATA**

Test #17615 Test Date 2/15/2017

**LUMINAIRE DATA**

Luminaire	CSL4-4040 tradeSELECT® CSL, Striplight 48" x 2.25" LED striplight with opal lens
Ballast	SL38-1900
Ballast Factor	1.00
Lamp	LED
Fixture Lumens	4517
Watts	40.24
Mounting	Recessed
Shielding Angle	0° = 90 90° = 90
Spacing Criterion	0° = 1.25 90° = 1.26
Luminous Opening in Feet	Length: 4.00 Width: 0.17 Height: 0.08

**ZONAL LUMEN SUMMARY**

Zone	Lumens	% Lamp	% Fixt.
0-30	998	22.1	22.1
0-40	1641	36.3	36.3
0-60	2957	65.5	65.5
0-90	4167	92.2	92.2
0-180	4517	100.0	100.0

**ENERGY DATA**

Total Luminaire Efficiency	100.0%
Total Lumens per Watt	112
IESNA RP-1-2004 Compliance	Non-Compliant
Comparative Yearly Lighting Energy Cost per 1000 Lumens	\$2.12 based on 3000 hrs. and \$0.08 per KWH

**INDOOR CANDELA PLOT**

