



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CT11BK50C Cable Tie CT11BK50-C, 10/Case *Minnesota Mining (3M)*

Catalog Number	CT11BK50C
Manufacturer	Minnesota Mining (3M)
Description	Cable Tie, 3 In;76.2 MM Bundle Diameter, Black, 11.1 In;282 MM Length, Made In Usa, Nylon 6/6 Material, +185°F;+85°C Maximum Operating Temperature, -40°C;-40°F Minimum Operating Temperature, 100 BG Package Quantity, Uv Resistant;Weather Resistant Resistance Properties, Culus Listed;Rohs Compliant;UI Listed 181B-C;UI Listed Type 21/Type 21S;UI Standard 62275;UI. File # E116841, Self-Adhesive Style, 22.68 KG;220 NM;50 LB Tensile Strength, 0.05 In;1.3 MM Thickness, 0.18 In;4.6 MM Width
Weight per unit	0.4300 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Attachment Type	expands in a fire to seal door frames and glazing applications to help prevent the passage of fire, smoke and toxic gases.
connector	expands in a fire to seal door frames and glazing applications to help prevent the passage of fire, smoke and toxic gases.

Dimensions and Weight

Size	expands in a fire to seal door frames and glazing applications to help prevent the passage of fire, smoke and toxic gases.
------	--

Descriptions

Description	CABLE TIE CT11BK50-C,10/CASE
extra long description	3M 7000058850 3M Standard Nylon Ca

Manufacturer Information

GTIN	00051128593004
Manufacturers Part Number	CT11BK50-C
UPC	051128593004

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	General Use

Availability

minimum qty	100
-------------	-----

Packaging

Carton	1000
Weight Per each	0.43

Uses, Certifications, and Standards

Application	Temflex
-------------	---------