

3M™ Standard Cable Ties

3M™ Standard Ties (50 lb., 220 N) - Plenum Rated

3M™ Standard Cable Ties are the most common sized ties and provide a standard level of performance for general-use holding applications up to 50 lb. Ties come in UV-resistant black for outdoor and indoor use as well as natural (white) nylon for an economical solution indoors.

Tensile Strength 50 lb (220 N)
Min. Operating Temp. -40°F (-40°C)
Max. Operating Temp. 185°F (85°C)
Min. Installation Temp. -4°F (-20°C)
RoHS 2011/65/EU Yes

Agency Approvals



Country of Origin



Order No.	UPC	Color	UV Resistance	Length	Width	Thickness	Max. Bundle Dia.	Tensile lbf. (N)	Items per Bag (Case)
CT8BK50-C	051128-59293	Black	Yes	7.60" (193 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	1.87" (47,5 mm)	50 (220)	100 (1000)
CT8BK50-M	051128-59294	Black	Yes	7.60" (193 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	1.87" (47,5 mm)	50 (220)	1000 (10,000)
CT8NT50-C	051128-59297	Natural	No	7.60" (193 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	1.87" (47,5 mm)	50 (220)	100 (1000)
CT8NT50-M	051128-59299	Natural	No	7.60" (193 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	1.87" (47,5 mm)	50 (220)	1000 (10,000)
CT8RD50-C	051128-59559	Red	No	7.60" (193 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	2.00" (50,8 mm)	50 (220)	100 (1000)
CT11BK50-C	051128-59300	Black	Yes	11.10" (282 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	3.00" (76,2 mm)	50 (220)	100 (1000)
CT11BK50-D	051128-59301	Black	Yes	11.10" (282 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	3.00" (76,2 mm)	50 (220)	500 (5000)
CT11NT50-C	051128-59302	Natural	No	11.10" (282 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	3.00" (76,2 mm)	50 (220)	100 (1000)
CT11NT50-D	051128-59303	Natural	No	11.10" (282 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	3.00" (76,2 mm)	50 (220)	500 (5000)
CT11RD50-C	051128-59560	Red	No	11.10" (282 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	3.00" (76,2 mm)	50 (220)	100 (1000)
CT15BK50-C	051128-59304	Black	Yes	14.60" (371 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	4.00" (101,6 mm)	50 (220)	100 (500)
CT15BK50-D	051128-59305	Black	Yes	14.60" (371 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	4.00" (101,6 mm)	50 (220)	500 (2500)
CT15NT50-C	051128-59307	Natural	No	14.60" (371 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	4.00" (101,6 mm)	50 (220)	100 (500)
CT15NT50-D	051128-59309	Natural	No	14.60" (371 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	4.00" (101,6 mm)	50 (220)	500 (2500)