

3M™ Standard Cable Ties - Weather-Resistant Black Nylon 6.6

Part Number	UPC	Length in (mm)	Width in (mm)	Thickness in (mm)	Max. Bundle Diameter in (mm)	Tensile lbf (N)	Min. Operating Temp °C (°F)	Max Operating Temp °C (°F)	Min. Installation Temp °C (°F)	Bag Qty.	Carton Qty.
Miniature Cable Ties (18 lb., 80 N) - Plenum Rated											
CT4BK18-C	051128-59273-1	4.1 (104)	0.10 (3,0)	0.04 (1,0)	0.75 (19)	18 (80)	-40 (-40)	85 (185)	0 (32)	100	1000
CT4BK18-M	051128-59274-8	4.1 (104)	0.10 (3,0)	0.04 (1,0)	0.75 (19)	18 (80)	-40 (-40)	85 (185)	0 (32)	1000	10000
CT6BK18-C	051128-59277-9	6.1 (155)	0.10 (3,0)	0.05 (1,3)	1.25 (32)	18 (80)	-40 (-40)	85 (185)	0 (32)	100	1000
CT8BK18-C	051128-59280-9	8.1 (206)	0.10 (3,0)	0.05 (1,3)	2.00 (51)	18 (80)	-40 (-40)	85 (185)	0 (32)	100	1000
CT8BK18-M	051128-59281-6	8.1 (206)	0.10 (3,0)	0.05 (1,3)	2.00 (51)	18 (80)	-40 (-40)	85 (185)	0 (32)	1000	10000
Intermediate Cable Ties (30-40 lb., 135-180 N) - Plenum Rated											
CT6BK30-C	051128-59284-7	5.8 (147)	0.14 (3,6)	0.05 (1,3)	1.25 (32)	30 (135)	-40 (-40)	85 (185)	-20 (-4)	100	1000
CT6BK30-M	051128-59285-4	5.8 (147)	0.14 (3,6)	0.05 (1,3)	1.25 (32)	30 (135)	-40 (-40)	85 (185)	-20 (-4)	1000	10000
CT8BK40-C	051128-59288-5	8.9 (226)	0.14 (3,6)	0.05 (1,3)	2.00 (51)	40 (180)	-40 (-40)	85 (185)	-20 (-4)	100	1000
CT8BK40-M	051128-59289-2	8.9 (226)	0.14 (3,6)	0.05 (1,3)	2.00 (51)	40 (180)	-40 (-40)	85 (185)	-20 (-4)	1000	10000
Standard Cable Ties (50 lb., 220 N) - Plenum Rated											
CT8BK50-C	051128-59293-9	7.6 (193)	0.18 (4,6)	0.05 (1,3)	1.87 (48)	50 (220)	-40 (-40)	85 (185)	-20 (-4)	100	1000
CT8BK50-M	051128-59294-6	7.6 (193)	0.18 (4,6)	0.05 (1,3)	1.87 (48)	50 (220)	-40 (-40)	85 (185)	-20 (-4)	1000	10000
CT11BK50-C	051128-59300-4	11.1 (282)	0.18 (4,6)	0.05 (1,3)	3.00 (76)	50 (220)	-40 (-40)	85 (185)	-20 (-4)	100	1000
CT11BK50-D	051128-59301-1	11.1 (282)	0.18 (4,6)	0.05 (1,3)	3.00 (76)	50 (220)	-40 (-40)	85 (185)	-20 (-4)	500	5000
CT15BK50-C	051128-59304-2	14.6 (371)	0.18 (4,6)	0.05 (1,3)	4.00 (102)	50 (220)	-40 (-40)	85 (185)	-20 (-4)	100	500
CT15BK50-D	051128-59305-9	14.6 (371)	0.18 (4,6)	0.05 (1,3)	4.00 (102)	50 (220)	-40 (-40)	85 (185)	-20 (-4)	500	2500
Light Heavy Duty Ties (120 lb., 550 N) - Plenum Rated											
CT8BK120-L	051128-59310-3	9 (229)	0.30 (7,6)	0.07 (1,8)	2.00 (51)	120 (530)	-40 (-40)	85 (185)	-20 (-4)	50	500
CT15BK120-C	051128-59312-7	15 (381)	0.30 (7,6)	0.07 (1,8)	4.00 (102)	120 (530)	-40 (-40)	85 (185)	-20 (-4)	100	500
CT15BK120-D	051128-59313-4	15 (381)	0.30 (7,6)	0.07 (1,8)	4.00 (102)	120 (530)	-40 (-40)	85 (185)	-20 (-4)	500	2500
Heavy Duty Ties (175 lb., 800 N)											
CT24BK175-L ¹	051128-59318-9	24 (610)	0.34 (8,6)	0.09 (2,3)	7.20 (183)	175 (800)	0 (32)	85 (185)	0 (32)	50	500
CT36BK175-L ^{1,2}	051128-59320-2	36 (914)	0.34 (8,6)	0.09 (2,3)	11.00 (279)	175 (800)	0 (32)	85 (185)	0 (32)	50	500
CT48BK175-L ²	051128-59322-6	47.9 (1217)	0.36 (9,1)	0.07 (1,8)	14.70 (373)	175 (800)	-	85 (185)	-	50	500
Screw Mountable - Plenum Rated											
CT8BK50S-C	051128-59292-2	8.6 (218)	0.18 (4,6)	0.06 (1,5)	2.00 (51)	50 (220)	-40 (-40)	85 (185)	-	100	1000
CT8BK50S-M	051128-59295-3	8.6 (218)	0.18 (4,6)	0.06 (1,5)	2.00 (51)	50 (220)	-40 (-40)	85 (185)	-	1000	10000

¹ Suitable for use in air handling spaces (plenum)

² UL Recognized