

## 3M™ Standard Cable Ties - Natural Nylon 6.6

Part Number	UPC	Length in (mm)	Width in (mm)	Thickness in (mm)	Max. Bundle Diameter in (mm)	Tensile lbf (N)	Min. Operating Temp °C (°F)	Max Operating Temp °C (°F)	Min. Installation Temp °C (°F)	Bag Qty.	Carton Qty.
<b>Intermediate Cable Ties (30-40 lb., 135-180 N) - Plenum Rated</b>											
CT6NT30-C	051128-59286-1	5.8 (147)	0.14 (3,6)	0.05 (1,3)	1.25 (32)	30 (135)	-40 (-40)	85 (185)	-20 (-4)	100	1000
CT6NT30-M	051128-59287-8	5.8 (147)	0.14 (3,6)	0.05 (1,3)	1.25 (32)	30(135)	-40 (-40)	85 (185)	-20 (-4)	1000	10000
CT8NT40-C	051128-59290-8	8.9 (226)	0.14 (3,6)	0.05 (1,3)	2.00 (51)	40 (180)	-40 (-40)	85 (185)	-20 (-4)	100	1000
CT8NT40-M	051128-59291-5	8.9 (226)	0.14 (3,6)	0.05 (1,3)	2.00 (51)	40 (180)	-40 (-40)	85 (185)	-20 (-4)	1000	10000
<b>Standard Cable Ties (50 lb., 220 N) - Plenum Rated</b>											
CT8NT50-C	051128-59297-7	7.6 (193)	0.18 (4,6)	0.05 (1,3)	1.87 (48)	50 (220)	-40 (-40)	85 (185)	-20 (-4)	100	1000
CT8NT50-M	051128-59299-1	7.6 (193)	0.18 (4,6)	0.05 (1,3)	1.87 (48)	50 (220)	-40 (-40)	85 (185)	-20 (-4)	1000	10000
CT8RD50-C	051128-59559-6	7.6 (193)	0.18 (4,6)	0.05 (1,3)	1.87 (48)	50 (220)	-40 (-40)	85 (185)	-20 (-4)	100	1000
CT11NT50-C	051128-59302-8	11.1 (282)	0.18 (4,6)	0.05 (1,3)	3.00 (76)	50 (220)	-40 (-40)	85 (185)	-20 (-4)	100	1000
CT11NT50-D	051128-59303-5	11.1 (282)	0.18 (4,6)	0.05 (1,3)	3.00 (76)	50 (220)	-40 (-40)	85 (185)	-20 (-4)	500	5000
CT11RD50-C	051128-59560-2	11.1 (282)	0.18 (4,6)	0.05 (1,3)	3.00 (76)	50 (220)	-40 (-40)	85 (185)	-20 (-4)	100	1000
CT15NT50-C	051128-59307-3	14.6 (371)	0.18 (4,6)	0.05 (1,3)	4.00 (102)	50 (220)	-40 (-40)	85 (185)	-20 (-4)	100	500
CT15NT50-D	051128-59309-7	14.6 (371)	0.18 (4,6)	0.05 (1,3)	4.00 (102)	50 (220)	-40 (-40)	85 (185)	-20 (-4)	500	2500
<b>Light Heavy Duty Ties (120 lb., 530 N) - Plenum Rated</b>											
CT8NT120-L	051128-59311-0	9 (229)	0.30 (7,6)	0.07 (1,8)	2.00 (51)	120 (530)	-40 (-40)	85 (185)	-20 (-4)	50	500
CT15NT120-C	051128-59315-8	15 (381)	0.30 (7,6)	0.07 (1,8)	4.00 (102)	120 (530)	-40 (-40)	85 (185)	-20 (-4)	100	500
CT15NT120-D	051128-59317-2	15 (381)	0.30 (7,6)	0.07 (1,8)	4.00 (102)	120 (530)	-40 (-40)	85 (185)	-20 (-4)	500	2500
<b>Heavy Duty Ties (175 lb., 800 N)</b>											
CT24NT175-L <sup>1</sup>	051128-59319-6	24 (610)	0.34 (8,6)	0.09 (2,3)	7.2 (183)	175 (800)	0 (32)	85 (185)	0 (32)	50	500
CT36NT175-L <sup>1,2</sup>	051128-59321-9	36 (914)	0.34 (8,6)	0.09 (2,3)	11.00 (279)	175 (800)	0 (32)	85 (185)	0 (32)	50	500
CT48NT175-L <sup>2</sup>	051128-59323-3	47.9 (1217)	0.36 (9,1)	0.07 (1,8)	14.70 (373)	175 (800)	-	85 (185)	-	50	500
<b>Screw Mountable<sup>1</sup> - Plenum Rated</b>											
CT8NT50S-C	051128-59296-0	8.6 (218)	0.18 (4,6)	0.06 (1,5)	2.00 (51)	50 (220)	-40 (-40)	85 (185)	-	100	1000
CT8NT50S-M	051128-59298-4	8.6 (218)	0.18 (4,6)	0.06 (1,5)	2.00 (51)	50 (220)	-40 (-40)	85 (185)	-	1000	10000
CT15NT50S-L	051128-59306-6	15.1 (384)	0.18 (4,6)	0.06 (1,5)	4.00 (102)	50 (220)	-40 (-40)	85 (185)	-	50	500
CT15NT50S-D	051128-59308-0	15.1 (384)	0.18 (4,6)	0.06 (1,5)	4.00 (102)	50 (220)	-40 (-40)	85 (185)	-	500	2500
CT15NT120S-D <sup>3</sup>	051128-59316-5	15.7 (399)	0.30 (7,6)	0.07 (1,8)	4.00 (102)	120 (530)	-40 (-40)	85 (185)	-	500	2500
CT15NT120S-L	051128-59314-1	15.7 (399)	0.30 (7,6)	0.07 (1,8)	4.00 (102)	120 (530)	-40 (-40)	85 (185)	-	50	500

<sup>1</sup> Suitable for use in air handling spaces (plenum)

<sup>2</sup> UL Recognized

<sup>3</sup> UL Listing is pending at this time