



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3325 Clay Avenue  
76711-0000, TX Waco  
Phone: 254-752-3331  
Fax: 254-752-3460



## CTH4040 3/0-4/0STR Cop C-Tap

*Nsi Industries*

Catalog Number	CTH4040
Manufacturer	Nsi Industries
Description	Heavy Duty Copper C Tap For 3/0 to 4/0 Awg Applications: Copper "C" Taps Are Range-Taking Compression Connectors Made From High Conductivity Copper Alloy. Ideal For Making Tap or Parallel Copper Connections From 8 Sol to 4/0 STR Conductors. Provides Consistent Reliability With Heavy Wall Construction That Prevents Relaxation Of The Joint After Installation. Installation Time Is Reduced Because Of Its "C" Shape. UI CU486A, 467 Suitable For Direct Burial and Csa Rated Electrical and Grounding.
Weight per unit	0.2500 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Conductor Size	(Run) 3/0-4/0 STR
Material	Copper
Tap Size	3/0-4/0 STR
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Copper
Finish	COPPER

### Dimensions and Weight

Size	L=.687 - W=1.00 - H=.625
------	--------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3325 Clay Avenue  
76711-0000, TX Waco  
Phone: 254-752-3331  
Fax: 254-752-3460

## Descriptions

Description	3/0-4/0STR COP C-TAP
extra long description	NSI CTH-4040 Copper C Tap 3/0 Str -
Features	Heavy Duty Copper C Tap for 3/0 to 4/0 AWG APPLICATIONS: Copper "C" Taps are range-taking compression connectors made from high conductivity copper alloy. Ideal for making tap or parallel copper connections from 8 SOL to 4/0 STR conductors. Provides consistent reliability with heavy wall construction that prevents relaxation of the joint after installation. Installation time is reduced because of its "C" shape. UL CU486A, 467 suitable for direct burial and CSA rated Electrical and Grounding.
Long Description	Heavy Duty Copper C Tap for 3/0 to 4/0 AWG APPLICATIONS: Copper "C" Taps are range-taking compression connectors made from high conductivity copper alloy. Ideal for making tap or parallel copper connections from 8 SOL to 4/0 STR conductors. Provides consistent reliability with heavy wall construction that prevents relaxation of the joint after installation. Installation time is reduced because of its "C" shape. UL CU486A, 467 suitable for direct burial and CSA rated Electrical and Grounding.
Product Type	Copper C Tap 3/0 STR - 4/0 STR Run & Tap
Special Features	(Run) 3/0-4/0 STR - (Tap) 3/0-4/0 STR

## Manufacturer Information

Brand	Polaris
GTIN	00662381022202
Manufacturers Part Number	CTH-4040
UPC	662381022202

## Taxonomies, Classifications, and Categories

Category Description	T&B C TAP LUGS
Type	Copper C Taps

## Packaging

Carton	1
Weight Per each	0.25

## Uses, Certifications, and Standards

Application	Terminate-Splice-Tap
environmental conditions	90 C
Temperature Rating	90 C