



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5668 N. Hwy 81
73533-0000, OK Duncan
Phone: 580-252-2582
Fax: 580-252-2738



CTH44 6SOL-4STR Cop C-Tap

Nsi Industries

Catalog Number	CTH44
Manufacturer	Nsi Industries
Description	Heavy Duty Copper C Tap Grounding Connector For 6 to 4 Awg Run - 6-6 Awg Tap Applications: Copper "C" Taps Are Range-Taking Compression Connectors Made From High Conductivity Copper Alloy. Ideal For Making Tap or Parallel Copper Connections From 8 Sol to 4/0 STR Conductors. Provides Consistent Reliability With Heavy Wall Construction That Prevents Relaxation Of The Joint After Installation. Installation Time Is Reduced Because Of Its "C" Shape. Ul CU486A, 467 Suitable For Direct Burial.
Weight per unit	0.0400 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Conductor Size	(Run) 6 SOL-4 STR
Material	Copper
Tap Size	4 SOL-4 STR
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Copper
Finish	COPPER

Dimensions and Weight

Size	L=.625 - W=.437 - H=.812
------	--------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5668 N. Hwy 81
73533-0000, OK Duncan
Phone: 580-252-2582
Fax: 580-252-2738

Descriptions

Description	6SOL-4STR COP C-TAP
extra long description	NSI CTH-44 C Tap Copper 6-4 Main 4-
Features	Heavy Duty Copper C Tap Grounding Connector for 6 to 4 AWG Run - 6-6 AWG Tap APPLICATIONS: Copper "C" Taps are range-taking compression connectors made from high conductivity copper alloy. Ideal for making tap or parallel copper connections from 8 SOL to 4/0 STR conductors. Provides consistent reliability with heavy wall construction that prevents relaxation of the joint after installation. Installation time is reduced because of its "C" shape. UL CU486A, 467 suitable for direct burial.
Long Description	Heavy Duty Copper C Tap Grounding Connector for 6 to 4 AWG Run - 6-6 AWG Tap APPLICATIONS: Copper "C" Taps are range-taking compression connectors made from high conductivity copper alloy. Ideal for making tap or parallel copper connections from 8 SOL to 4/0 STR conductors. Provides consistent reliability with heavy wall construction that prevents relaxation of the joint after installation. Installation time is reduced because of its "C" shape. UL CU486A, 467 suitable for direct burial.
Product Type	C Tap Copper 6-4 Main 4-4 Tap
Special Features	(Run) 6 SOL-4 STR - (Tap) 4 SOL-4 STR

Manufacturer Information

Brand	Polaris
GTIN	00662381022158
Manufacturers Part Number	CTH-44
UPC	662381022158

Taxonomies, Classifications, and Categories

Category Description	T&B C TAP LUGS
Type	Copper C Taps

Packaging

Carton	1
Package	25
Weight Per each	0.04

Uses, Certifications, and Standards

Application	Terminate-Splice-Tap
environmental conditions	90 C
Temperature Rating	90 C