

Eaton CV2125XMM

Catalog Number: CV2125XMM

Eaton Type CV Molded Case Circuit Breaker, Molded case circuit breaker, 125 A, 65 kAIC, Two-pole, 120/240 V, #6 - 4/0 Al/Cu, CV, #4/0 kcmil maximum load, Includes mounting kit



Photo is representative

General specifications

Product Name	Catalog Number
Eaton CCV tenant main breaker	CV2125XMM
UPC	Product Length/Depth
786685706450	7.5 in
Product Height	Product Width
5 in	3.5 in
Product Weight	Warranty
2.75 lb	Limited lifetime
Certifications	
UL 489	
CSA Std. C22.2 No. 5	

Type

Molded case circuit breaker

Amperage Rating

125 A

Voltage rating

120/240 V

Circuit breaker frame type

CV

Accessories

Includes mounting kit

Terminals

#4/0 kcmil maximum load

Interrupt rating

65 kAIC

Wire size

#6-4/0 AWG Cu/Al

Number of poles

Two-pole

Brochures

Type CV Molded-case circuit breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Specifications and datasheets

Eaton Specification Sheet - CV2125XMM



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia