

# Eaton CVS2100XMM

Catalog Number: CVS2100XMM

Eaton Type CV Molded Case Circuit Breaker, Molded case circuit breaker, 100 A, 42 kAIC, Two-pole, #6 - 4/0 Al/Cu, CV, #4/0 kcmil maximum load, Includes mounting kit



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CCV tenant main breaker	CVS2100XMM
<b>UPC</b>	<b>Product Length/Depth</b>
786685705880	7.5 in
<b>Product Height</b>	<b>Product Width</b>
5 in	3.5 in
<b>Product Weight</b>	<b>Warranty</b>
2.75 lb	Limited lifetime
<b>Certifications</b>	
UL 489	
CSA Std. C22.2 No. 5	

Type

Molded case circuit breaker

Amperage Rating

100 A

Circuit breaker frame type

CV

Accessories

Includes mounting kit

Terminals

#4/0 kcmil maximum load

Interrupt rating

42 kAIC

Wire size

#6-4/0 AWG Cu/Al

Number of poles

Two-pole

Brochures

Type CV Molded-case circuit breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Specifications and datasheets

Eaton Specification Sheet - CVS2100XMM



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia