



Long Nose Pliers, Insulated, 8-Inch



Klein Tools Insulated Long Nose Side-Cutting pliers are 1000V rated for safety on the job. The long nose is designed to grab and loop wire. Dual layer, orange-over-white insulation provides a warning sign that insulation may be compromised. The molded insulation meets or exceeds ASTM F1505-16 and IEC 60900:2012 standards for insulated tools. Cutting knives are induction hardened for long life.

Specifications

Type:	Long Nose Side Cutting Pliers	Application:	For Work Near Energized Sources
Special Features:	Flame Retardant and Impact Resistant Handle	Overall Length:	8.91" (22.6 cm)
Material:	Induction Hardened Steel	Jaw Length:	2.32" (5.9 cm)
Jaw Width:	1.02" (2.6 cm)	Jaw Thickness:	0.5" (1.3 cm)
Point Diameter:	0.125" (0.32 cm)	Cutting Knives:	Standard
Knife Length:	0.693" (1.8 cm)	Cut Style:	Side-Cutting
Joint Type:	Hot-Riveted	Handle Color:	Orange
Handle Finish:	2-Layer Insulation	Handle Length:	5.625" (14.3 cm)
Insulated:	Yes	Standard:	IEC 60900 and ASTM F1505
Weight:	11.2 oz (318 g)		